

## Product data sheet

### Characteristics

# PDL56PAV416

## Plug - Angled, 16A, 500V, 4-Round Pin, Resistant Orange



### Main

Range	56 Series
Product or component type	Plug

### Complementary

Rated current	16 A
[Ue] rated operational voltage	500 V
Material	PBT (polybutylene terephthalate)
Colour tint	Orange
Surface finish	Gloss
Network frequency	50 Hz
Network number of phases	3 phases
Pin number	4
Ambient air temperature for operation	-40...55 °C
Cable cross section	7...16 mm <sup>2</sup>
Quantity per set	Set of 4
Type of packing	Carton

### Environment

IP degree of protection	IP66
-------------------------	------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	9.5 cm
Package 1 Length	17 cm
Package 1 Weight	281 g

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations