

Product data sheet

Characteristics

PDL56PAV516

Plug - Angled, 16A, 500V, 5-Round Pin, Resistant Orange



Main

Range	56 Series
Product or component type	Plug

Complementary

Rated current	16 A
[Ue] rated operational voltage	500 V
Material	PBT (polybutylene terephthalate)
Colour tint	Orange
Surface finish	Gloss
Network frequency	50 Hz
Network number of phases	3 phases
Pin number	5
Ambient air temperature for operation	-40...55 °C
Cable cross section	7...16 mm ²
Quantity per set	Set of 4
Type of packing	Carton




Environment

IP degree of protection	IP66
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.339 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

