

Product data sheet

Characteristics

PDL56PB10TLEGY

56 Series - push button BLE time delay switch - 10AX - 15A - 240V - less enclosure - grey



Main

Range of product	56 Series™
Product or component type	Time switch
Colour tint	Grey
Quantity per set	Set of 4
Type of packing	Carton

Complementary

Control type	Electronic
Material	PC (polycarbonate) UV stabilised
Surface finish	Gloss
Installation direction	Vertical
Length	94 mm
Width	94 mm
Depth	76.5 mm
Dimension type	External
[Ue] rated operational voltage	220/240 V 50 Hz
Rated current	15 A 10 AX
Network number of phases	1 phase
Number of gangs	1 gang
Number of poles	1
Device mounting	Surface
Fixing center	84 mm

Environment

Ambient air temperature for operation	0...25 °C
IP degree of protection	IP66

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.