

## Product data sheet

### Characteristics

# PDL56PB10TLEGY

## Clipsal - 56 Series, Time Delay Switch Push Button, 10A Bluetooth IP66, Grey



### Main

Range of product	56 Series™
Product or component type	Time switch
Colour tint	Grey
Quantity per set	Set of 4
Type of packing	Carton

### Complementary

Control type	Electronic
Material	PC (polycarbonate) UV stabilised
Surface finish	Gloss
Installation direction	Vertical
Length	94 mm
Width	94 mm
Depth	76.5 mm
Dimension type	External
[Ue] rated operational voltage	220/240 V 50 Hz
Rated current	15 A 10 AX
Network number of phases	1 phase
Number of gangs	1 gang
Number of poles	1
Device mounting	Surface
Fixing center	84 mm

### Environment

Ambient air temperature for operation	0...25 °C
IP degree of protection	IP66

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	9.6 cm
Package 1 Length	9.6 cm
Package 1 Weight	464 g

### Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------