



### Main

Range of product	56 Series
Product or component type	Push-button switch
Control type	Push-button latching
Colour tint	Grey

### Complementary

Material	PC (polycarbonate)
Surface finish	Gloss
Installation direction	Horizontal/vertical
Width	95 mm
Height	95 mm
Depth	20 mm
[In] rated current	16 A
[Ue] rated operational voltage	250 V
Network frequency	50 Hz
Network number of phases	1 phase
Number of gangs	1 gang
Device mounting	Surface
Fixing center	84 x 84 mm
IP degree of protection	IP67
Ambient air temperature for operation	-40...55 °C
Cable cross section	0.75...6 mm <sup>2</sup>
Auxiliary contact composition	1 NO/NC
Quantity per set	Set of 8
Type of packing	Carton

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4 cm
Package 1 Width	9.5 cm
Package 1 Length	9.5 cm
Package 1 Weight	121 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations