

Product data sheet

Characteristics

PDL56PV716

Plug - Straight, 16A, 500V, 7-Round Pin, Resistant Orange

Main

Range	56 Series
Product or component type	Plug

Complementary

Rated current	16 A
[Ue] rated operational voltage	500 V
Material	PBT (polybutylene terephthalate)
Colour tint	Orange
Surface finish	Gloss
Network frequency	50 Hz
Network number of phases	3 phases
Pin number	7
Ambient air temperature for operation	-40...55 °C
Cable cross section	1...6 mm ²
Quantity per set	Set of 4
Type of packing	Carton

Environment

IP degree of protection	IP66
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.354 kg

Offer Sustainability

EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations