

Product data sheet

Characteristics

PDL56SO3102LEGY

Socket, 16A, 110V, 1-Gang, 3-Round Pin, Yellow



Main

Range of product	56 Series™
Product brand	PDL
Product or component type	Socket-outlet
Quantity per set	Set of 4
Type of packing	Carton

Complementary

Material	Polycarbonate
Colour tint	Grey
Surface finish	Gloss
Installation direction	Vertical
Width	95 mm
Height	95 mm
Depth	35 mm
Rated current	10 A
[Ue] rated operational voltage	250 V
Network frequency	50 Hz
Network number of phases	1 phase
Number of gangs	1 gang
Pin number	3
Device composition	Flat pin
Mounting mode	Surface mounted
Fixing center	84 x 84 mm
Cable cross section	0.75...6 mm²


Environment

IP degree of protection	IP66
Ambient air temperature for operation	-40...55 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5 cm
Package 1 Width	9.5 cm
Package 1 Length	19 cm
Package 1 Weight	365 g

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes