

Product data sheet

Characteristics

PDL56SO315LECG

56 Series Socket - 3 Pin - 15A - 250V - Less Enclosure - Chemical Grey



Main

Product or component type	Socket-outlet
Device short name	PDL56SO315LECG
Plug, socket category	Low voltage
Poles description	1P + N + E
Network type	AC
Outlet standard	Australian/New Zealand




Complementary

Mounting mode	Surface mounted
Plug, socket, control station shape	Straight
[In] rated current	15 A
Pin number	3 pins
Shape of pin	Flat
[Ue] rated operational voltage	250 V
Network frequency	50 Hz
Material	Polycarbonate: cover
Contacts material	Pins: brass
Connections - terminals	Screw terminals 1.5...6 mm ² rigid or stranded cable
Wire stripping length	10 mm
Net weight	0.185 kg
Height	95.0 mm
Width	95.0 mm
Depth	60.0 mm
Colour	Dark grey

Environment

Standards	AS/NZS 3123
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C
Ambient air temperature for storage	-25...75 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation

 [China RoHS Declaration](#)

Environmental Disclosure

 [Product Environmental Profile](#)
