

## Product data sheet

### Characteristics

# PDL56SO316/240LERW

Socket - Twin, 10A, 250V, 2-Gang, 3- Flat Pin, Resistant Orange



### Main

Range of product	56 Series™
Product brand	PDL
Product or component type	Socket-outlet
Quantity per set	Set of 2
Type of packing	Carton

### Complementary

Material	PC + PET
Colour tint	White
Surface finish	Gloss
Installation direction	Vertical
Width	95 mm
Height	191 mm
Depth	35 mm
Rated current	16 A
[Ue] rated operational voltage	250 V
Network frequency	50 Hz
Network number of phases	1 phase
Number of gangs	2 gangs
Pin number	3
Device composition	Round pin
Mounting mode	Surface mounted
Fixing center	84 x 84 mm
Cable cross section	0.75...10 mm²

### Environment

IP degree of protection	IP66
Ambient air temperature for operation	-40...55 °C

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	9.5 cm
Package 1 Length	19.1 cm
Package 1 Weight	230.484 g

Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>