

Product data sheet

Characteristics

PDL56SO720LEGY

Socket, 20A, 500V, 1-Gang, 7- Round Pin, Grey

Main

Range of product	56 Series™
Product brand	PDL
Product or component type	Socket-outlet
Quantity per set	Set of 4
Type of packing	Carton

Complementary

Material	Polycarbonate
Colour tint	Grey
Surface finish	Gloss
Installation direction	Vertical
Width	95 mm
Height	95 mm
Depth	35 mm
Rated current	20 A
[Ue] rated operational voltage	500 V
Network frequency	50 Hz
Network number of phases	3 phases
Number of gangs	1 gang
Pin number	7
Device composition	Round pin
Mounting mode	Surface mounted
Fixing center	84 x 84 mm
Cable cross section	1...10 mm ²

Environment

IP degree of protection	IP66
Ambient air temperature for operation	-40...55 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6 cm
Package 1 Width	9.5 cm
Package 1 Length	9.5 cm
Package 1 Weight	278 g

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes