

Product data sheet

Characteristics

PDL56SS10WE

Switch - Sunset Photoelectric, 10A, 240V, 1-Gang, White

Main

Range of product	56 Series™
Product or component type	Switch
Control type	Electronic

Complementary

Material	PVC + PC (polycarbonate)
Colour tint	Grey and opal
Surface finish	Gloss
Installation direction	Horizontal Vertical
Width	95 mm
Height	95 mm
Depth	43 mm
Rated current	10 A
[Ue] rated operational voltage	230/240 V
Network frequency	50 Hz
Mounting mode	Surface mounted
IP degree of protection	IP66
Ambient air temperature for operation	-10...45 °C
Cable cross section	0.75...6 mm ²
Quantity per set	Set of 1
Type of packing	Carton

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.5 cm
Package 1 Width	11.5 cm
Package 1 Length	10.5 cm
Package 1 Weight	0.374 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	2