

## Product data sheet

### Characteristics

# PDL56SW1102ILEGY

Switch - Intermediate Changeover, 10A, 240V, Grey



### Main

Range of product	56 Series™
Product or component type	Rotary switch
Colour tint	Grey
Motor M-rating AS3133	M40
Quantity per set	Set of 4
Type of packing	Carton

### Complementary

Control type	Rotary
Material	PC (polycarbonate)
Surface finish	Gloss
Installation direction	Vertical
Width	95 mm
Height	95 mm
Depth	49 mm
Rated current	10 A
[Ue] rated operational voltage	240 V
Network frequency	50 Hz
Network number of phases	1 phase
Number of gangs	1 gang
Mounting mode	Surface mounted
Fixing center	84 x 84 mm
Cable cross section	0.75...6 mm <sup>2</sup>

### Environment

IP degree of protection	IP66
Ambient air temperature for operation	-40...55 °C

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	9.5 cm
Package 1 Length	9.5 cm
Package 1 Weight	164 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations