

Product data sheet

Characteristics

PDL56SW1102LECG

56 Series, Switch, 2-Way 10A 240V 1-Pole IP66, Chemical-Resistant Grey



Main

Device short name	PDL56SW1102LECG
Product or component type	Switch
Poles description	1P
Control type	Rotary knob
Rotary handle padlocking	2 padlocks 8 mm

Complementary

[Ue] rated operational voltage	250 V AC 50 Hz
[Ithe] conventional enclosed thermal current	10 A
Connections - terminals	Screw terminals cable(s) 1.5...6 mm ² rigid or stranded
Height	95.0 mm
Width	95.0 mm
Depth	62.0 mm
Net weight	0.164 kg
Colour	Body: grey Rotary handle: dark grey




Environment

Standards	AS/NZS 3133
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	9.5 cm
Package 1 Length	9.5 cm
Package 1 Weight	159 g

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes