

Product data sheet

Characteristics

PDL56SW250LEGY

Switch, 50A, 500V, 2-Pole, Grey



Main

Range of product	56 Series™
Product or component type	Rotary switch
Colour tint	Grey
Motor M-rating AS3133	M250
Quantity per set	Set of 4
Type of packing	Carton

Complementary

Number of poles	2
Control type	Rotary
Material	PC (polycarbonate)
Surface finish	Gloss
Installation direction	Vertical
Width	95 mm
Height	95 mm
Depth	62 mm
Rated current	50 A
[Ue] rated operational voltage	415 V
Network frequency	50 Hz
Network number of phases	1 phase
Number of gangs	1 gang
Mounting mode	Surface mounted
Fixing center	84 x 84 mm
Cable cross section	6...35 mm ²




Environment

IP degree of protection	IP66
Ambient air temperature for operation	-40...55 °C

Packing Units

Package 1 Weight	0.327 kg
------------------	----------

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	 RECh Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
