

Product data sheet

Characteristics

PDL56SW420/2KGLERW

Switch - KG Series, 20A, 500V, 4-Pole, 2-Gang, Resistant White



Main

Range of product	56 Series™
Product or component type	Rotary switch
Colour tint	White
Quantity per set	Set of 4
Type of packing	Carton

Complementary

Number of poles	4
Control type	Rotary
Material	PBT (polybutylene terephthalate)
Surface finish	Gloss
Installation direction	Vertical
Width	95 mm
Height	190 mm
Depth	66 mm
Rated current	20 A
[Ue] rated operational voltage	500 V
[Ui] rated insulation voltage	690 V
Network frequency	50 Hz
Network number of phases	3 phases
Number of gangs	2 gangs
Mounting mode	Surface mounted
Fixing center	180 X 84 mm
Cable cross section	1...6 mm ²

Environment

IP degree of protection	IP66
Ambient air temperature for operation	-40...55 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	19 cm
Package 1 Width	9.5 cm
Package 1 Length	6.6 cm
Package 1 Weight	195.5 g

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant with Exemptions
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations