

## Product data sheet

### Characteristics

# PDL56SW4202KGLGY

## Switch - KG Series, 20A, 500V, 4-Pole, 2-Gang, Grey



### Main

Range of product	56 Series™
Product or component type	Rotary switch
Colour tint	Grey
Quantity per set	Set of 4
Type of packing	Carton

### Complementary

Number of poles	4
Control type	Rotary
Material	PC (polycarbonate)
Surface finish	Gloss
Installation direction	Vertical
Width	95 mm
Height	190 mm
Depth	66 mm
Rated current	20 A
[Ue] rated operational voltage	500 V
[Ui] rated insulation voltage	690 V
Network frequency	50 Hz
Network number of phases	3 phases
Number of gangs	2 gangs
Mounting mode	Surface mounted
Fixing center	180 X 84 mm
Cable cross section	1...6 mm <sup>2</sup>

### Environment

IP degree of protection	IP66
Ambient air temperature for operation	-40...55 °C

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	19 cm
Package 1 Width	9.5 cm
Package 1 Length	6.6 cm
Package 1 Weight	195.5 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations