

Product data sheet

Characteristics

PDL56SWB3322KGLGY

Switch - Base Mount, 32A, 415V, 3-Pole, 2-Gang, Grey

Main

Range of product	56 Series™
Product or component type	Rotary switch
Control type	Rotary

Complementary

Material	PC (polycarbonate)
Colour tint	Grey
Surface finish	Gloss
Installation direction	Vertical
Width	95 mm
Height	190 mm
Depth	66 mm
Rated current	32 A
[Ue] rated operational voltage	240 V
Nominal power	11 KW 7.5 kW
Utilisation category	AC-3 AC-23A
Network frequency	50 Hz
Motor M-rating AS3133	M180
Number of gangs	2 gangs
Number of poles	3
Mounting mode	Surface mounted
Fixing center	180 X 84 mm
IP degree of protection	IP66
Ambient air temperature for operation	-40...55 °C
Cable cross section	6 mm ²
Quantity per set	Set of 1
Type of packing	Carton

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.5 cm
Package 1 Width	10.5 cm
Package 1 Length	21.3 cm
Package 1 Weight	0.462 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes