

# Product data sheet

## Characteristics

# PDL56SWB3632KGLGY

## Switch - Base Mount, 63A, 415V, 3-Pole, 2-Gang, Grey

### Main

Range of product	56 Series™
Product or component type	Rotary switch
Control type	Rotary

### Complementary

Material	PC (polycarbonate)
Colour tint	Grey
Surface finish	Gloss
Installation direction	Vertical
Width	95 mm
Height	190 mm
Depth	66 mm
Rated current	63 A
[Ue] rated operational voltage	240 V
Nominal power	18.5 KW 22 kW
Utilisation category	AC-21A AC-3
Network frequency	50 Hz
Motor M-rating AS3133	M300
Number of gangs	2 gangs
Number of poles	3
Mounting mode	Surface mounted
Fixing center	180 X 84 mm
IP degree of protection	IP66
Ambient air temperature for operation	-40...55 °C
Cable cross section	16 mm²
Quantity per set	Set of 1
Type of packing	Carton

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.5 cm
Package 1 Width	10.5 cm
Package 1 Length	21.5 cm
Package 1 Weight	0.484 kg

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>