

Product data sheet

Characteristics

PDL56SWK320LEGY

Switch - Keylock, 20A, 415V, 3-Pole, Grey

Main

| | |
|---------------------------|---------------|
| Range of product | 56 Series™ |
| Product or component type | Rotary switch |
| Colour tint | Grey |
| Motor M-rating AS3133 | M150 |
| Quantity per set | Set of 4 |
| Type of packing | Carton |

Complementary

| | |
|--------------------------------|------------------------|
| Number of poles | 3 |
| Control type | Rotary |
| Material | PC (polycarbonate) |
| Surface finish | Gloss |
| Installation direction | Vertical |
| Width | 95 mm |
| Height | 95 mm |
| Depth | 73 mm |
| Rated current | 20 A |
| [Ue] rated operational voltage | 415 V |
| [Ui] rated insulation voltage | 660 V |
| Network frequency | 50 Hz |
| Network number of phases | 3 phases |
| Number of gangs | 1 gang |
| Mounting mode | Surface mounted |
| Fixing center | 84 x 84 mm |
| Cable cross section | 1...16 mm ² |

Environment

| | |
|---------------------------------------|-------------|
| IP degree of protection | IP66 |
| Ambient air temperature for operation | -40...55 °C |

Packing Units

| | |
|------------------------------|--------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 7 cm |
| Package 1 Width | 9.5 cm |
| Package 1 Length | 9.5 cm |
| Package 1 Weight | 268 g |

Offer Sustainability

| | |
|---|---|
| Packaging without single use plastic | No |
| Packaging made with recycled cardboard | Yes |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant with Exemptions |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |
| Take-back | No |
| Carbon footprint (kg.eq.CO2 per CR, Total Life cycle) | 6 |