

Product data sheet

Characteristics

PDL56SWK350LEGY

Switch - Keylock, 50A, 415V, 3-Pole, Grey

Main

| | |
|---------------------------|---------------|
| Range of product | 56 Series™ |
| Product or component type | Rotary switch |
| Colour tint | Grey |
| Motor M-rating AS3133 | M250 |
| Quantity per set | Set of 4 |
| Type of packing | Carton |

Complementary

| | |
|--------------------------------|------------------------|
| Number of poles | 3 |
| Control type | Rotary |
| Material | PC (polycarbonate) |
| Surface finish | Gloss |
| Installation direction | Vertical |
| Width | 95 mm |
| Height | 95 mm |
| Depth | 68 mm |
| Rated current | 50 A |
| [Ue] rated operational voltage | 415 V |
| [Ui] rated insulation voltage | 660 V |
| Network frequency | 50 Hz |
| Network number of phases | 3 phases |
| Number of gangs | 1 gang |
| Mounting mode | Surface mounted |
| Fixing center | 84 x 84 mm |
| Cable cross section | 6...35 mm ² |

Environment



| | |
|---------------------------------------|-------------|
| IP degree of protection | IP66 |
| Ambient air temperature for operation | -40...55 °C |

Packing Units

| | |
|------------------------------|------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 1 kg |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

| | |
|----------------------------|--|
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| Mercury free | Yes |
| China RoHS Regulation |  China RoHS Declaration |
| RoHS exemption information |  Yes |