

## Product data sheet

### Characteristics

# PDL581M16CPT

## 1-Way Switch Module With Gold Plated Contacts; 250VAC/28VDC, White



### Main

Range of product	500 Series
Product or component type	Switch
Quantity per set	Set of 20
Type of packing	Carton
Colour tint	White
Motor M-rating AS3133	M50

### Complementary

Control type	Rocker
Material	PC (polycarbonate)
Installation direction	Horizontal/vertical
Surface finish	Gloss
Width	23 mm
Height	23 mm
Depth	24 mm
Rated current	16 A/16 AX 5A
[Ue] rated operational voltage	250 V AC 50 Hz 28 V DC
Network number of phases	1 phase
Number of poles	1
Connections - terminals	Screw terminal

### Environment

Ambient air temperature for operation	-10...40 °C
---------------------------------------	-------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	2.5 cm
Package 1 Length	3 cm
Package 1 Weight	0.011 kg

### Offer Sustainability

EU RoHS Directive	Under investigation
Circularity Profile	No need of specific recycling operations