

Product data sheet

Characteristics

PDL592FWH

Double Switched Socket Outlet; 10A, 230/240VAC, Vertical Mount, White



Main

Range of product	500 Series
Product or component type	Socket
Colour tint	White
Quantity per set	Set of 10
Type of packing	Carton

Complementary

Control type	Rocker
Material	PC (polycarbonate)
Installation direction	Vertical
Surface finish	Gloss
Width	74 mm
Height	118 mm
[Ie] rated operational current	10 A
[Ue] rated operational voltage	220/240 V 50 Hz
Network number of phases	1 phase
Number of gangs	2 gangs
Connections - terminals	3 x 2.5 mm ² terminals
Number of poles	2
Device mounting	Surface
Fixing center	84 mm

Environment

Ambient air temperature for operation	-10...40 °C
---------------------------------------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	7.5 cm
Package 1 Length	11.7 cm
Package 1 Weight	101 g

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations