

Product data sheet

Characteristics

PDL596PM30

Plate-Mounted RCD; 20A, 230 - 240VAC, 30mA Trip

Main

Range of product	500 Series
Product or component type	Residual current device
Colour tint	White
Quantity per set	Set of 1 Set of 100
Type of packing	Polybag

Complementary

Control type	Push-button
Material	PC (polycarbonate)
Installation direction	Vertical
Surface finish	Gloss
Width	56 mm
Height	92 mm
[Ie] rated operational current	20 A
[Ue] rated operational voltage	230/240 V 50 Hz
Network number of phases	1 phase
Number of poles	2
Device mounting	Surface
Fixing center	84 mm
Clamping connection capacity	3 x 2.5 mm ²




Environment

Ambient air temperature for operation	-10...40 °C
---------------------------------------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	120.000 g

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes