

Product data sheet

Characteristics

PDL610TML24RD

Illuminated Module With Small LED; 20mA, 24VDC, White Module, Red



Main

Range of product	600 Series
Product or component type	Switch

Complementary

Material	PC (polycarbonate)
Light source colour	Red
Surface finish	Opaque
Installation direction	Vertical
Length	21 mm
Width	20 mm
Depth	9.3 mm
[Ue] rated operational voltage	24 V
Network number of phases	1 phase
Number of gangs	1 gang
Mounting mode	Front
Number of terminals	2
Cut-out dimensions	25 mm
Quantity per set	Set of 20
Type of packing	Crate

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.1 cm
Package 1 Width	2 cm
Package 1 Length	0.9 cm
Package 1 Weight	0.004 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations