

Product data sheet

Characteristics

PDL611MWH

Adapter Clip; White

Main

Range of product	600 Series
Product or component type	Data jack adaptor

Complementary

Fixing mode	By clips
Product compatibility	LexCom modular jack
Material	PC (polycarbonate)
Colour tint	White
Surface finish	Gloss
Installation direction	Vertical Horizontal
Width	23 mm
Height	23 mm
Depth	10 mm
Mounting mode	Front
Ambient air temperature for operation	-10...40 °C
Quantity per set	Set of 100
Type of packing	Carton

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.3 cm
Package 1 Width	2.5 cm
Package 1 Length	2.5 cm
Package 1 Weight	1.46 g
Unit Type of Package 2	BB1
Number of Units in Package 2	100
Package 2 Height	7.7 cm
Package 2 Width	12 cm
Package 2 Length	19.5 cm
Package 2 Weight	146 g

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Take-back	No