

Product data sheet

Characteristics

PDL624TMWH

Dimmer 600 Series Module - Rotary - 240 V - White



Main

Range of product	600 Series
Product or component type	Switch
Dimmer control	Rotary

Complementary

Material	PC (polycarbonate)
Colour tint	White
Surface finish	Gloss
Installation direction	Vertical
Length	23 mm
Width	23 mm
Rated current	20 A 16 AX
[Ue] rated operational voltage	220/240 V
Network frequency	50 Hz
Power range	20 W 450 W
Load interrupting current	0.18 A 0.1 A
Motor M-rating AS3133	M60
Network number of phases	1 phase
Number of gangs	1 gang
Mounting mode	Front
Ambient air temperature for operation	0...40 °C
Quantity per set	Set of 10
Type of packing	Carton

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7 cm
Package 1 Width	4 cm
Package 1 Length	10 cm
Package 1 Weight	40 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information