

## Product data sheet

### Characteristics

# PDL625FMWH

## Fan Speed Controller Module; 20A/16AX/M60, 220 - 240VAC, 50 Hz, White



### Main

Range of product	600 Series
Product or component type	Switch

### Complementary

Control type	Rotary knob
Material	PC (polycarbonate)
Colour tint	White
Surface finish	Gloss
Installation direction	Vertical
Length	23 mm
Width	23 mm
Rated current	20 A 16 AX
[Ue] rated operational voltage	220/240 V
Network frequency	50 Hz
Motor M-rating AS3133	M60
Network number of phases	1 phase
Number of gangs	1 gang
Number of poles	1
Mounting mode	Front
Fixing center	84 mm
Ambient air temperature for operation	0...40 °C
Quantity per set	Set of 10
Type of packing	Carton

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5 cm
Package 1 Width	4 cm
Package 1 Length	9 cm
Package 1 Weight	42.3 g

## Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>