

Product data sheet

Characteristics

PDL642MUSBWH

USB Charger Module; 80mA Input, 1.2A Output, 230 - 240VAC, White



Main

Range of product	600 Series
Product or component type	USB charger + socket-outlet

Complementary

Material	PC (polycarbonate)
Colour tint	White
Surface finish	Gloss
Installation direction	Horizontal Vertical
Length	23 mm
Width	23 mm
Input current	80 mA
Number output current	1.2 A
[Ue] rated operational voltage	230/240 V

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	10 cm
Package 1 Length	11 cm
Package 1 Weight	44 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	7.7 cm
Package 2 Width	12 cm
Package 2 Length	19.5 cm
Package 2 Weight	620 g
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Height	24 cm
Package 3 Width	29 cm
Package 3 Length	33 cm
Package 3 Weight	6.62 kg

Offer Sustainability

EU RoHS Directive	Not compliant
-------------------	---------------