

Product data sheet

Characteristics

PDL644CWH

Cover Plate Quad Switched Socket, 600 Series, 4-Gang Horizontal



Main

Range of product	600 Series
Product or component type	Cover plate
Colour tint	White
Quantity per set	Set of 10
Type of packing	Carton

Complementary

Product destination	4 gangs horizontal switched socket
Material	PC (polycarbonate)
Surface finish	Gloss
Installation direction	Horizontal
Width	191 mm
Height	79 mm
Mounting mode	Surface mounted

Environment

Ambient air temperature for operation	-10...40 °C
---------------------------------------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.3 cm
Package 1 Width	8 cm
Package 1 Length	19 cm
Package 1 Weight	0.022 kg

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations