

## Product data sheet

### Characteristics

# PDL647WH

## Switch 600 Series, Assembled, Vertical, 1-gang, 250V 40A, white



### Main

Range of product	600 Series
Product or component type	Switch
Control type	Rocker

### Complementary

Material	PC (polycarbonate)
Colour tint	White
Surface finish	Gloss
Installation direction	Vertical
Length	74 mm
Width	118 mm
Rated current	40 A
[Ue] rated operational voltage	250 V
Network type	AC
Motor M-rating AS3133	M180
Network number of phases	2 phases
Number of gangs	1 gang
Number of poles	2
Mounting mode	Surface mounted
Fixing center	84 mm
Ambient air temperature for operation	-10...40 °C
Cable cross section	2 x 6 mm <sup>2</sup>

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4 cm
Package 1 Width	7.5 cm
Package 1 Length	12 cm
Package 1 Weight	141 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations