

Product data sheet

Characteristics

PDL654MWH

600 Series, Module Universal Dimmer, Rotary Switch, 450W Leading/Trailing, White



Main

Range of product	600 Series
Product or component type	Switch
Dimmer control	Rotary




Complementary

Material	PC (polycarbonate)
Colour tint	White
Surface finish	Gloss
Installation direction	Vertical
Length	23 mm
Width	23 mm
Rated current	16 AX
[Ue] rated operational voltage	220/240 V
Network frequency	50 Hz
Power range	450 W 20 W
Load interrupting current	0.18 A 0.1 A
Mounting mode	Front
Ambient air temperature for operation	0...40 °C
Relative humidity	10...90 %
Quantity per set	Set of 10
Type of packing	Carton

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	8 cm
Package 1 Length	11 cm
Package 1 Weight	43 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information