

## Product data sheet

### Characteristics

# PDL654WH

## Dimmer 600 Series Module - Universal - Rotary - Integrated Switch - 250 V - White

### Main

Range of product	600 Series
Product or component type	Switch
Dimmer control	Rotary push type

### Complementary

Material	PC (polycarbonate)
Colour tint	White
Surface finish	Gloss
Installation direction	Vertical
Length	118 mm
Width	74 mm
Rated current	16 AX
[Ue] rated operational voltage	230/250 V
Network frequency	50 Hz
Network number of phases	1 phase
Number of gangs	1 gang
Mounting mode	Surface mounted
Fixing center	84 mm
Ambient air temperature for operation	-10...40 °C
Cable cross section	2 x 2.5 mm <sup>2</sup> 4 x 1.5 mm <sup>2</sup>
Quantity per set	Set of 1
Type of packing	Carton

### Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.