

Product data sheet

Characteristics

PDL675WH

Universal Vertical/Horizontal Shaver Socket Outlet, White



Main

Range of product	600 Series
Product or component type	Shaver socket-outlet insert

Complementary

Material	PC (polycarbonate)
Colour tint	White
Surface finish	Gloss
Installation direction	Vertical Horizontal
Width	118 mm
Height	74 mm
[Ue] rated operational voltage	115/240 V
Network frequency	50 Hz
Number of gangs	1 gang
Mounting mode	Surface mounted
Fixing center	84 mm
Ambient air temperature for operation	-10...40 °C
Cable cross section	2.5 mm ²
Quantity per set	Set of 1
Type of packing	Carton

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.0 cm
Package 1 Width	7.7 cm
Package 1 Length	11.8 cm
Package 1 Weight	651.0 g

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes