

## Product data sheet

### Characteristics

# PDL680M32HWH

Switch 600 Series Mechanism - Single-pole -  
1-gang - Marked HOB-OFF - 250 V - 32 A / 20  
AX - White



### Main

Range of product	600 Series
Product or component type	Switch
Control type	Rocker

### Complementary

Material	PA (polyamide)
Colour tint	White
Surface finish	Gloss
Installation direction	Vertical
Length	23 mm
Width	23 mm
Rated current	32 A 20 AX
[Ue] rated operational voltage	250 V
Network type	AC
Motor M-rating AS3133	M180
Number of gangs	1 gang
Number of poles	1
Mounting mode	Front
Ambient air temperature for operation	-10...40 °C
Cable cross section	2 x 6 mm <sup>2</sup>

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	19 g
Package 1 Height	25 mm
Package 1 width	25 mm
Package 1 Length	35 mm

### Offer Sustainability

EU RoHS Directive	Under investigation
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>