

Product data sheet

Characteristics

PDL680M32HWH

Switch 600 Series Mechanism - Single-pole - 1-gang - Marked HOB-OFF - 250 V - 32 A / 20 AX - White



Main

Range of product	600 Series
Product or component type	Switch
Control type	Rocker

Complementary

Material	PA (polyamide)
Colour tint	White
Surface finish	Gloss
Installation direction	Vertical
Length	23 mm
Width	23 mm
Rated current	32 A 20 AX
[Ue] rated operational voltage	250 V
Network type	AC
Motor M-rating AS3133	M180
Number of gangs	1 gang
Number of poles	1
Mounting mode	Front
Ambient air temperature for operation	-10...40 °C
Cable cross section	2 x 6 mm ²

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	2.5 cm
Package 1 Length	2.5 cm
Package 1 Weight	19.385 g

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations