

Product data sheet

Characteristics

PDL680M32IOWH

680M32IO WHITE ON/OFF 32A MOD



Main

Range of product	600 Series
Product or component type	Switch
Control type	Rocker

Complementary

Material	PA (polyamide)
Colour tint	White
Surface finish	Gloss
Installation direction	Vertical
Length	23 mm
Width	23 mm
Rated current	20 AX 32 A
[Ue] rated operational voltage	250 V
Network type	AC
Motor M-rating AS3133	M180
Number of gangs	1 gang
Number of poles	1
Mounting mode	Front
Ambient air temperature for operation	-10...40 °C
Cable cross section	2 x 6 mm ²

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	2.5 cm
Package 1 Length	3.5 cm
Package 1 Weight	0.019 kg

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

