

# Product data sheet

## Characteristics

# PDL681M16HFPWH

## 681m16hfp Wh Hing Sw Mod Press



### Main

Range of product	600 Series
Product or component type	Switch
Control type	Rocker

### Complementary

Material	PC (polycarbonate)
Colour tint	White
Surface finish	Gloss
Installation direction	Vertical Horizontal
Rated current	16 A 8 AX 16 AX
[Ue] rated operational voltage	230/240 V
Network type	AC
Motor M-rating AS3133	M50
Number of poles	1
Cable cross section	2 x 2.5 mm <sup>2</sup> 4 x 1.5 mm <sup>2</sup>

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.3 cm
Package 1 Width	3.17 cm
Package 1 Length	2.3 cm
Package 1 Weight	0.015 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 Yes
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations