

Product data sheet

Characteristics

PDL681M20FGWH

Switch 600 Series Mechanism - Single-pole - 1-gang - Marked OFF-FRIDGE - 250 V - 20 A / 16 AX - White

Main

Range of product	600 Series
Product or component type	Switch
Control type	Rocker

Complementary

Material	PC (polycarbonate)
Colour tint	White
Surface finish	Gloss
Installation direction	Horizontal Vertical
Length	23 mm
Width	23 mm
Depth	26 mm
Rated current	16 AX 20 A
[Ue] rated operational voltage	250 V
Network type	AC
Motor M-rating AS3133	M60
Network number of phases	1 phase
Number of gangs	1 gang
Number of poles	1
Mounting mode	Front
Ambient air temperature for operation	-10...40 °C
Cable cross section	2 x 2.5 mm ² 4 x 1.5 mm ²
Load type	LEDi lamp 250 W

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	2.3 cm
Package 1 Length	2.3 cm
Package 1 Weight	14 g

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Take-back	No