

## Product data sheet

### Characteristics

# PDL683VWPWH

## 2-Way Vertical Waterproof Switch; 16A/16AX/ M50, 3-Gang, 1P, White



### Main

Range of product	600 Series
Product or component type	Switch
Control type	Rocker



### Complementary

Material	PC (polycarbonate)
Colour tint	White
Surface finish	Gloss
Installation direction	Vertical
Length	74 mm
Width	118 mm
Rated current	20 A 16 AX
[Ue] rated operational voltage	250 V
Network type	AC
Motor M-rating AS3133	M50
Number of gangs	3 gangs
Number of poles	1
Mounting mode	Surface mounted
Fixing center	84 mm
Ambient air temperature for operation	-10...40 °C

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.2 cm
Package 1 Width	7.8 cm
Package 1 Length	5.0 cm
Package 1 Weight	143.0 g

### Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 Yes