

### Main

Range of product	600 Series
Product or component type	Switch
Colour tint	White



### Complementary

Material	PC (polycarbonate)
Surface finish	Glossy
Installation direction	Horizontal Vertical
Length	100 mm
Width	48 mm
Height	12 mm
Number of gangs	1 gang
Device mounting	Surface
Fixing center	80 mm
Ambient air temperature for operation	-10...40 °C
Quantity per set	Set of 200 Set of 10
Type of packing	Carton

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.5 cm
Package 1 Width	5 cm
Package 1 Length	10 cm
Package 1 Weight	36 g

### Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	 Yes

---

China RoHS Regulation

 [China RoHS Declaration](#)

---

Take-back

No

---