

Product data sheet

Characteristics

PDL691RCD30WH

600 Series, Switched Socket, 10A RCD 30mA Trip, White



Main

Range of product	600 Series
Product or component type	Residual current device


Complementary

Control type	Push-button
Material	PC (polycarbonate)
Colour tint	White
Surface finish	Gloss
Installation direction	Vertical
Width	74 mm
Height	118 mm
Rated current	10 A
[Ue] rated operational voltage	230/240 V
Network frequency	50 Hz
Network number of phases	1 phase
Number of poles	2
Mounting mode	Surface mounted
Fixing center	84 mm
Cable cross section	3 x 2.5 mm ²
Quantity per set	Set of 1
Type of packing	Carton

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.0 cm
Package 1 Width	7.7 cm
Package 1 Length	12.0 cm
Package 1 Weight	0.221 kg

Offer Sustainability

EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes