

Product data sheet

Characteristics

PDL691WH

Socket Outlet 600 Series - Single switched - Assembled - Vertical - 250 V - 10 A - White



Main

Range of product	600 Series
Product or component type	Switched socket

Complementary

Control type	Rocker
Material	PC (polycarbonate)
Colour tint	White
Surface finish	Gloss
Installation direction	Vertical
Width	74 mm
Height	118 mm
[Ue] rated operational voltage	250 V 50 Hz
Device mounting	Surface
Number of gangs	1 gang
Fixing center	84 mm
Ambient air temperature for operation	-10...40 °C
Cable cross section	3 x 2.5 mm ²
Cut-out dimensions	50 mm
Quantity per set	Set of 10
Type of packing	Carton

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	7 cm
Package 1 Length	12 cm
Package 1 Weight	0.083 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	120 cm
Package 2 Width	153 cm
Package 2 Length	160 cm
Package 2 Weight	1.07 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations