

## Product data sheet

### Characteristics

# PDL692IDWH

## 600 Series, Double Switched Socket and Circuit Identification, Vertical



### Main

Range of product	600 Series
Product or component type	Switched socket

### Complementary

Control type	Rocker
Material	PC (polycarbonate)
Colour tint	White
Surface finish	Gloss
Installation direction	Vertical
Width	74 mm
Height	118 mm
[Ue] rated operational voltage	250 V 50 Hz
Device mounting	Surface
Fixing center	84 mm
Ambient air temperature for operation	-10...40 °C
Cable cross section	3 x 2.5 mm <sup>2</sup>
Quantity per set	Set of 5
Type of packing	Carton

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	7.0 cm
Package 1 Length	11.5 cm
Package 1 Weight	96.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	15
Package 2 Height	7.5 cm
Package 2 Width	19 cm
Package 2 Length	44 cm
Package 2 Weight	1.5 kg
Package 3 Height	7.5 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations