

Product data sheet

Characteristics

PDL695RCD10WH

Socket Outlet 600 Series - Twin switched - Assembled - Horizontal - RCD protection - 240 V - 10 A - White



Main

Range of product	600 Series
Product or component type	Residual current device

Complementary

Control type	Push-button
Material	PC (polycarbonate)
Colour tint	White
Surface finish	Gloss
Installation direction	Horizontal
Width	118 mm
Height	74 mm
Rated current	10 A
[Ue] rated operational voltage	230/240 V
Network frequency	50 Hz
Network number of phases	1 phase
Number of poles	2
Mounting mode	Surface mounted
Fixing center	84 mm
Cable cross section	3 x 2.5 mm ²
Quantity per set	Set of 1
Type of packing	Carton

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.9 cm
Package 1 Width	7.7 cm
Package 1 Length	7.0 cm
Package 1 Weight	207.3 g

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes