

## Product data sheet

### Characteristics

# PDL699TBWH

## Socket Outlet 600 Series - Twin switched - Assembled - Horizontal - Worktop - 250 V - 10 A - White



### Main

Range of product	600 Series
Product or component type	Switched socket

### Complementary

Control type	Rocker
Material	PC (polycarbonate)
Colour tint	White
Surface finish	Gloss
Installation direction	Horizontal
Length	167 mm
Height	45 mm
Dimension type	External
[Ue] rated operational voltage	230/240 V 50 Hz
Device mounting	Surface
Number of gangs	2 gangs
Fixing center	138 x 150 mm
Ambient air temperature for operation	-10...40 °C
Cable cross section	3 x 2.5 mm <sup>2</sup>
Cut-out dimensions	50 mm
Quantity per set	Set of 10
Type of packing	Carton

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4 cm
Package 1 Width	4.5 cm
Package 1 Length	17 cm
Package 1 Weight	132 g

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations