

Product data sheet

Characteristics

PDL824MWH

Dimmer Control Module;25 - 400W, Electronic Trailing Edge Control, White



Main

Range of product	Modena 800 Series
Product or component type	Dimmer
Control type	Rotary knob

Complementary

Material	PC (polycarbonate)
Colour tint	White
Surface finish	Matt
Installation direction	Vertical Horizontal
Width	25 mm
Height	45 mm
Rated current	16 AX
[Ue] rated operational voltage	230/240 V
Network frequency	50 Hz
Nominal power	0.45 kW
Network number of phases	1 phase
Number of gangs	1 gang
Mounting mode	Front
Quantity per set	Set of 5
Type of packing	Carton

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	7.5 cm
Package 1 Length	10.5 cm
Package 1 Weight	0.044 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information