

Product data sheet

Characteristics

PDL825FMWH

Modular Fan Speed Controller

Module;230-240VAC and 250VAC Switch, 50 Hz, White



Main

Range of product	Modena 800 Series
Product or component type	Fan controller
Control type	Rotary knob


Complementary

Material	PC (polycarbonate)
Colour tint	White
Surface finish	Matt
Installation direction	Horizontal Vertical
Width	25 mm
Height	45 mm
Rated current	16 AX
[Ue] rated operational voltage	230/250 V
Load type	40...500 W 0.16...2 A for motor
Network frequency	50 Hz
Network number of phases	1 phase
Number of gangs	1 gang
Mounting mode	Front
Quantity per set	Set of 10
Type of packing	Plastic bag and carton

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	10.5 cm
Package 1 Length	15 cm
Package 1 Weight	0.044 kg

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
-------------------	--