

Product data sheet

Characteristics

PDL854MWH

Universal Dimmer Control Module;20 - 450W, Lead/Trail Edge Phase Control, White



Main

Range of product	Modena 800 Series
Product or component type	Dimmer
Control type	Rotary knob

Complementary

Material	PC (polycarbonate)
Colour tint	White
Surface finish	Matt
Installation direction	Horizontal Vertical
Width	124 mm
Height	85 mm
Rated current	16 AX
[Ue] rated operational voltage	230/240 V
Network frequency	50 Hz
Nominal power	0.45 kW
Network number of phases	1 phase
Number of gangs	1 gang
Mounting mode	Front
Ambient air temperature for operation	-10...40 °C
Relative humidity	10...90 %
Quantity per set	Set of 8
Type of packing	Carton

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	7.5 cm
Package 1 Length	10.5 cm
Package 1 Weight	45 g

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.