

Product data sheet

Characteristics

PDL854WH

Universal Dimmer Switch; 20 - 450W, White



Main

Range of product	Modena 800 Series
Product or component type	Dimmer
Control type	Rotary knob

Complementary

Material	PC (polycarbonate)
Colour tint	White
Surface finish	Glossy and matt
Installation direction	Horizontal
Width	124 mm
Height	85 mm
Depth	9 mm
Rated current	16 AX
[Ue] rated operational voltage	230/240 V
Network frequency	50 Hz
Nominal power	0.45 kW
Network number of phases	1 phase
Number of gangs	1 gang
Mounting mode	Surface mounted
Fixing center	84 mm
Ambient air temperature for operation	-10...40 °C
Relative humidity	10...90 %
Quantity per set	Set of 8
Type of packing	Carton

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.129 kg

Offer Sustainability

EU RoHS Directive	Under investigation
Circularity Profile	No need of specific recycling operations