

Product data sheet

Characteristics

PDL854WH

Universal Dimmer Switch; 20 - 450W, White



Main

| | |
|---------------------------|-------------------|
| Range of product | Modena 800 Series |
| Product or component type | Dimmer |
| Control type | Rotary knob |

Complementary

| | |
|---------------------------------------|--------------------|
| Material | PC (polycarbonate) |
| Colour tint | White |
| Surface finish | Glossy and matt |
| Installation direction | Horizontal |
| Width | 124 mm |
| Height | 85 mm |
| Depth | 9 mm |
| Rated current | 16 AX |
| [Ue] rated operational voltage | 230/240 V |
| Network frequency | 50 Hz |
| Nominal power | 0.45 kW |
| Network number of phases | 1 phase |
| Number of gangs | 1 gang |
| Mounting mode | Surface mounted |
| Fixing center | 84 mm |
| Ambient air temperature for operation | -10...40 °C |
| Relative humidity | 10...90 % |
| Quantity per set | Set of 8 |
| Type of packing | Carton |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 0.129 kg |

Offer Sustainability

| | |
|---------------------|--|
| EU RoHS Directive | Under investigation |
| Circularity Profile | No need of specific recycling operations |